
TENAX GRIFON

Mono-oriented polyethylene net. Thanks to its special production process, it is a light, competitive product, highly tear and mechanic resistant.



Picture out of scale

| PHYSICAL CHARACTERISTICS | TEST METHOD | UNIT | GRIFON | NOTES |
|--------------------------|----------------|------|-------------|-------|
| POLYMER TYPE | | | HDPE | - |
| MESH SHAPE | | | RECTANGULAR | - |
| COLOUR | | | ORANGE | - |

| DIMENSIONAL CHARACTERISTICS | TEST METHOD | UNIT | GRI | FON | NOTES |
|-----------------------------|----------------|------|--------|------|---------------|
| MD PITCH | | mm | 75.0 | | а |
| UNIT WEIGHT | | g/m² | 75.0 | | - |
| WIDTH | | m | 1.0 | 1.2 | = |
| ROLL LENGTH | | m | 50.0 | 50.0 | - |
| ROLL DIAMETER | | m | 0.13 | 0.13 | - |
| ROLL VOLUME | | m³ | 0.017 | 0.02 | - |
| ROLL WEIGHT | | kg | 4.0 | 4.7 | - |
| INNER PACKAGING | | | PE BAG | | |
| OUTER PACKAGING | | | | - | - |

| TECHNICAL CHARACTERISTICS | TEST METHOD | UNIT | GRIFON | NOTES |
|---------------------------|----------------|------|--------|-------|
| TENSILE STRENGTH MD | METHOD TX3 | kN/m | 2.5 | a, b |
| ELONGATION MD | METHOD TX3 | % | 15.0 | a, b |

NOTES:

- a) MD: machine direction
- b) TX3: 300 mm/min

The data contained in this publication are based on the knowledge available at the time of printing and may be subjected to amendments due to changes of the methods of testing and/or manufacturing. All dimensions are reported as typical values.

Tenax nets are thermoplastic products subjected to shrinkage. MD: longitudinal direction. TD: transversal direction.

Tenax Spa Quality System has been assessed and registered in agreement with ISO 9001:2008 Standard.

GEN 894,4 - E - 03/17



TENAX SpA
Via dell'Industria, 3
23897 Viganò (LC)
Tel. +39 039.9219300
Fax +39 039.9219290
customer.service@tenax.net



