

Purchasing Process



Decide your tabletop size



Select (Non) vibration isolators
(Table standard 85 cm height)



Dark Room



Shelf Accessories

How to choose the right tables

Choose table size and table thickness

Optical tables are offered in an array of sizes, both imperial and metric to meet many application needs. The size ranges from 60cm x 90 cm (2ft x 3 ft) to 300cm x 240cm (10ft x 8ft) Each table series is offered in two imperial and two metric thickness. The thicker tables are stiffer, yielding a higher resonant frequency, from 2.5 cm to 20cm. Customized sizes and joined configuration can also be manufactured to meet your needs.

Determine Vibration or Non-vibration

OP Mount offers three series of vibration isolators and one type of NonVibration isolator to meet virtually all requirements.

Determine Table Height

OP Mount simplifies the table height selection to be 85 cm as the standard and most common used height. Customers may also request for other desirable heights to meet their own needs.

Add desired options (for customized tables)

We offers several standard options including laser parts, mounting for accessory shelves, black finish. Customized cutouts and hole patterns are easily accommodated. We can also provides special heights for our wide range of isolators.

4



OTB-series A.19

4



OTC-series A.20

Vibration Performance Inspection

In order to strictly inspects all optical table after manufactured to assure the vibration achieves the best performance, Op Mount Purchase a new software to inspect each Optical Table.

