

# AK HR Series

## High Rejection Low Energy Brackish Water RO Elements

The A-Series proprietary thin-film reverse osmosis membrane elements are characterized by high flux and high sodium chloride rejection. AK HR low pressure brackish elements are selected when high rejection and low operating pressures are desired. These elements allow significant energy savings since good rejection is achieved at operating pressures as low as 100 psig (689 kPa).

These elements are recommended for low brackish water with salt concentration (TDS) levels up to 5,000mg/l. In turn, AK HR elements produce a permeate quality close to a standard brackish membrane element at a much lower pressure.

**Table 1: Element Specification**

Membrane	Thin-film membrane (TFM*)		
Model	Average permeate flow gpd (m3/day) <sup>1,2</sup>	Average NaCl rejection <sup>1,2</sup>	Minimum NaCl rejection <sup>1,2</sup>
AK-90	2200 (8.3)	99.5%	99.0%
AK-365	9600 (36.3)	99.5%	99.0%
AK-400	10500 (39.7)	99.5%	99.0%
AK-440	11500 (43.5)	99.5%	99.0%

<sup>1</sup>Average salt rejection after 24 hours operation. Individual flow rate may vary +25%/-15%.

<sup>2</sup>Testing conditions: 500ppm NaCl solution at 115psi (793kPa) operating pressure, 77°F (25°C), pH7.5 and 15% recovery.


Model	Active area ft <sup>2</sup> (m <sup>2</sup> )	Outer wrap	Part number
AK-90	90 (8.4)	Fiberglass	3056678
AK-365	365 (33.9)	Fiberglass	3056679
AK-400	400 (37.2)	Fiberglass	3056680
AK-440	440 (40.9)	Fiberglass	3056681

**Table 2: Operating and CIP parameters**


<b>Typical Operating Pressure</b>	120 psi (830 kPa)
<b>Typical Operating Flux</b>	10-20GFD (15-35LMH)
<b>Maximum Operating Pressure</b>	400 psi (2,758 kPa)
<b>Maximum Temperature</b>	Continuous operation: 122°F (50°C) Clean-In-Place (CIP): 122°F (50°C)
<b>pH range</b>	Optimum rejection pH: 7.0-7.5, Continuous operation: 4.0-11.0, Clean-In-Place (CIP): 2.0-11.5
<b>Maximum Pressure Drop</b>	Over an element: 12 psi (83 kPa) Per housing: 50 psi (345 kPa)
<b>Chlorine Tolerance</b>	1,000+ ppm-hours, dechlorination recommended
<b>Feedwater<sup>3</sup></b>	NTU < 1 SDI < 5

<sup>3</sup>SDI is measured on a non-linear scale using a 0.45 micron filter paper. Additionally, finer colloids, particulates and microorganisms that pass through the filter paper and not measured in the SDI test, will potentially foul the RO element. For performance consistency and project warranty, please use Winflows projection software and consult your Filters with Membranes representative.

**Figure 1a: Element Dimensions Diagram – Male**



**Figure 1b: Element Dimensions Diagram – Female**



Find a contact near you by visiting [www.gewater.com](http://www.gewater.com) and clicking on "Contact Us".

\* Trademark of General Electric Company; may be registered in one or more countries.

©2014, General Electric Company. All rights reserved.



**Table 3: Dimensions and Weights**

Model <sup>1</sup>	Type	Dimensions, inches (cm)			Boxed Weight lbs (kg)
		A	B <sup>2</sup>	C	
AK-90	Male	40.0 (101.6)	0.75 (1.90)	3.9 (9.9)	9 (4)
AK-365	Female	40.0 (101.6)	1.125 (2.86)	7.9 (20.1)	35 (16)
AK-400	Female	40.0 (101.6)	1.125 (2.86)	7.9 (20.1)	35 (16)
AK-440	Female	40.0 (101.6)	1.125 (2.86)	7.9 (20.1)	35 (16)